

Product data sheet

Characteristics

QOM2E2200NRB

Main breaker, QO, 200A, 2 pole, 120/240 VAC, 22 kA, bolt on mount, enclosed, NEMA 3R

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Circuit breaker
Range	QO
Current Rating	200 A
Voltage Rating	120/240 V AC
Mounting Type	Bolt-on
Number of Poles	2P
Electrical Connection	Lugs
Frame Size	QOM2

Complementary

Interrupt Rating	22 kA 120/240 V AC 50/60 Hz
Provided Equipment	enclosure
Wire Size	AWG 4...300 kcmil aluminium/copper
Tightening Torque	53.10 lbf.in (6 N.m) 0.01...0.10 in ² (4...65 mm ²) AWG 12...AWG 2/0
Height	24.55 in (623.57 mm)
Width	8.68 in (220.47 mm)
Load Center Type	Main breaker
Number of Phases	1 phase
Indoor/Outdoor Use	Outdoor

Environment

Certifications	UL Listed
Ambient Rating	104 °F (40 °C)
NEMA Enclosure Rating	NEMA 3R

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	00100 - QOM-VH MAIN CB
Discount Schedule	DE3A
GTIN	00785901375302
Nbr. of units in pkg.	1
Package weight(Lbs)	16.25 lb(US) (7.37 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	25.70 in (65.278 cm)
Package 1 width	9.60 in (24.384 cm)
Package 1 Length	6.00 in (15.24 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	42
Package 2 Weight	730.00 lb(US) (331.122 kg)
Package 2 Height	48.00 in (121.92 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------