

# Product data sheet

## Characteristics

# QOT2020

Tandem mini circuit breaker, QO, 2 x 1 pole at 20A, 120/240 VAC, 10 kA, plug in mount

Product availability : Stock - Normally stocked in distribution facility



### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Tandem
Ratings	HACR rated
Electrical Connection	Pressure plate

### Complementary

Interrupt Rating	10 kA 120/240 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper AWG 12...AWG 8 aluminium
Tightening Torque	44.25 lbf.in (5 N.m) 0.02...0.04 in <sup>2</sup> (10...25 mm <sup>2</sup> ) AWG 8...AWG 2)
Height	3.22 in (81.79 mm)
Depth	2.91 in (73.91 mm)
Width	0.75 in (19.05 mm)

### Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

Category	00004 - QO,QOT 10-30A 1P;10-60A 2P
Discount Schedule	DE2A
GTIN	00785901418085
Nbr. of units in pkg.	10
Package weight(Lbs)	10 lb(US) (4.54 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.30 in (8.382 cm)
Package 1 width	0.70 in (1.778 cm)
Package 1 Length	3.40 in (8.636 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	3.36 lb(US) (1.524 kg)
Package 2 Height	3.80 in (9.652 cm)
Package 2 width	0.70 in (1.778 cm)
Package 2 Length	7.60 in (19.304 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	34.95 lb(US) (15.853 kg)
Package 3 Height	8.20 in (20.828 cm)
Package 3 width	8.30 in (21.082 cm)
Package 3 Length	19.80 in (50.292 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------

Dimensions

