

# RSL1PVFU

Harmony, Slim interface relay pre-assembled, 6 A, 1 CO, with LED, with protection circuit, screw connectors, 60 V DC

Product availability : Stock - Normally stocked in distribution facility



## Main

Range of product	Harmony Electromechanical Relays
Series name	Interface relay
Product or component type	Pre-assembled plug-in relay with socket
Device short name	RSL
Contacts type and composition	1 C/O
Contact operation	Standard
[Uc] control circuit voltage	60 V DC
[Ithe] conventional enclosed thermal current	6 A -40...131 °F (-40...55 °C)
Status LED	With
Shape of pin	Flat (PCB type)

## Complementary

Fixing mode	Plastic compression spring
Average resistance	20500 Ohm DC 23 °C +/- 10 %
[Ui] rated insulation voltage	250 V EN/IEC 277 V cUL
[Uimp] rated impulse withstand voltage	6 kV IEC
Contacts material	Silver alloy (AgSnO2)
[Ie] rated operational current	6 A 1 C/O AC-1/DC-1)IEC/UL
Minimum switching current	100 mA
Maximum switching voltage	277 V
Switching voltage	12 V
Maximum switching capacity	1500 VA 150 W
Minimum switching capacity	120 mW
Operating rate	<= 72000 cycles/hour no-load <= 360 cycles/hour under load
Mechanical durability	10000000 cycles

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Electrical durability	60000 cycles resistive, 6 A 250 V, AC-1
Operating time	5 ms reset 12 ms
Reset time	20 ms
Marking	CE
Protection category	RT III
Test levels	Level A
Operating position	Any position
Height	3.09 in (78.6 mm)
Width	0.24 in (6.2 mm)
Depth	3.74 in (95 mm)
Terminals description ISO n°1	(A1-A2)CO (11-12-14)OC
Sale per indivisible quantity	10
Net Weight	0.06 lb(US) (0.029 kg)
Load current	6 A 250 V AC 0.5 mm mounting distance
Average coil consumption	0.17 W, DC
Drop-out voltage threshold	>= 0.05 Uc
Contact terminal arrangement	Separate
Connections - terminals	Screw connectors, 1 x 0.2...1 x 2.5 mm <sup>2</sup> AWG 24...AWG 14) flexible with cable end Screw connectors, 1 x 0.2...1 x 2.5 mm <sup>2</sup> AWG 24...AWG 14) solid without cable end
Tightening torque	< 0.5 N.m M2.5
Safety reliability data	B10d = 60000
Control type	Without push-button
Mounting support	35 mm symmetrical DIN rail
Device presentation	Complete product

## Environment

Input voltage	110 V AC/DC 88...126.5 V)
Dielectric strength	1000 V AC between contacts 4000 V AC between coil and contact
Standards	CSA C22.2 No 14 EN/IEC 61810-1 UL 508
Product certifications	CSA UL GOST
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Vibration resistance	10 gn +/- 1 mm 10...150 Hz)10 cycles not operating EN/IEC 60068-2-6 5 gn +/- 1 mm 10...150 Hz)10 cycles in operation EN/IEC 60068-2-6
IP degree of protection	IP40 conforming to EN/IEC 60529
Shock resistance	10 gn 11 ms) in operation EN/IEC 60068-2-27 5 gn 11 ms) not operating EN/IEC 60068-2-27
Ambient air temperature for operation	-40...158 °F (-40...70 °C)

## Ordering and shipping details

Category	21127 - ZELIO ICE CUBE RELAYS
Discount Schedule	CP2
GTIN	00785901834748
Nbr. of units in pkg.	10
Package weight(Lbs)	0.07 lb(US) (0.03 kg)
Returnability	Yes
Country of origin	CN

## Packing Units

Package 1 Height	0.070 dm
Package 1 width	0.800 dm
Package 1 Length	0.970 dm

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------

Dimensions

