

Product availability : Stock - Normally stocked in distribution facility



Main

Range of product	Powerpact
Circuit breaker type	Standard

Complementary

Tightening torque	12.39 lbf.in (1.4 N.m)
Width	1.28 in (32.51 mm)
Depth	1.24 in (31.50 mm)
Height	1.72 in (43.69 mm)

Ordering and shipping details

Category	01103 - H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
GTIN	00785901712282
Nbr. of units in pkg.	1
Package weight(Lbs)	0.29 lb(US) (0.13 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	1.80 in (4.572 cm)
Package 1 width	2.50 in (6.350 cm)
Package 1 Length	3.20 in (8.128 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
------------------	-----------------------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------