

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Undervoltage trip
Breaking capacity code	JD HJ LD LR DG LL JR DL DJ JJ HG JL LJ HL LG JG HD HR

Complementary

Rated voltage	24 V AC
Tightening torque	12.39 lbf.in (1.4 N.m) 0.00...0.00 in ² (0.82...2.5 mm ²) AWG 18...AWG 14)

Environment

Product certifications	CSA UL Listed
------------------------	------------------

Ordering and shipping details

Category	01103 - H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
GTIN	00785901597179
Package weight(Lbs)	0.32 lb(US) (0.15 kg)
Returnability	Yes
Country of origin	US

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------