

Product data sheet

Characteristics

SDSA1175

Surge protection device, Surgellogic, 36kA, 120/240 VAC, 1 phase, 3 wire, 25kA SCCR, NEMA 4X

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Surge protection device
Range	Surgellogic

Complementary

Surge Current	36 kA per phase
Voltage Rating	120/240 V AC
Number of Phases	1 phase
Wiring Configuration	3-wire
MCOV	150 V
Nominal Discharge Current	10 kA
SCCR	25 kA
Local Signalling	Status LED green normal operation
Height	2.25 in (57.15 mm)
Width	2.25 in (57.15 mm)
Depth	2.7 in (68.58 mm)
Cable length	24 in (609.60 mm)

Environment

Enclosure Rating	NEMA 4X
Enclosure Material	Black Plastic
Standards	UL 1449:ed. 4: type I NEC 285 CSA C22.2 No 8
Ambient Operating	149 °F (65 °C)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	08462 - SURGE PROTECTION SDSA
Discount Schedule	DE1B
GTIN	00785901210870
Nbr. of units in pkg.	20
Package weight(Lbs)	0.7 lb(US) (0.32 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.60 in (6.604 cm)
Package 1 width	2.70 in (6.858 cm)
Package 1 Length	6.80 in (17.272 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Weight	14.46 lb(US) (6.559 kg)
Package 2 Height	7.40 in (18.796 cm)
Package 2 width	10.80 in (27.432 cm)
Package 2 Length	13.10 in (33.274 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

