

Product data sheet

Characteristics

SDSA2040

Surge protection device, Surgelogic, 40kA, 208Y/120 VAC, 3 phase, 4 wire, NEMA 4X

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Surge protection device
Range	Surgelogic

Complementary

Surge Current	40 kA
Voltage Rating	208Y/120 V AC
Number of Phases	3 phase
Wiring Configuration	4-wire
Connection	Wire AWG 12 copper
MCOV	180 V
Nominal Discharge Current	10 kA
SCCR	200 kA
Local Signalling	Status LED normal operation
Mounting Support	Panel mounting
Height	3.07 in (78 mm)
Width	3.62 in (92 mm)
Depth	2.64 in (67 mm)
Cable length	24 in (609.60 mm)

Environment

Enclosure Rating	NEMA 4X
Enclosure Material	Black plastic
Standards	UL 1449:ed. 4 CSA C22.2 No 8:1986
Ambient Operating	149 °F (65 °C)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	08462 - SURGE PROTECTION SDSA
Discount Schedule	DE1B
GTIN	00785901602569
Package weight(Lbs)	0.98 lb(US) (0.44 kg)
Returnability	Yes
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Approximate Dimensions

