

Product data sheet

Characteristics

SDSA2040D

Surge Protect - 40kA - 240VAC delta - 3P3W - T4X

Product availability : Stock - Normally stocked in distribution facility



Main

| | |
|---------|-------------------------|
| Product | Surge protection device |
|---------|-------------------------|

Complementary

| | |
|---------------------------|-----------------------------|
| Surge Current | 40 kA |
| Voltage Rating | 240 V delta AC |
| Number of Phases | 3 phase |
| Wiring Configuration | 3-wire |
| Connection | Wire AWG 12 copper |
| MCOV | 180 V |
| Nominal Discharge Current | 10 kA |
| SCCR | 200 kA |
| Local Signalling | Status LED normal operation |
| Mounting Support | Panel mounting |
| Height | 3.07 in (78 mm) |
| Width | 3.62 in (92 mm) |
| Depth | 2.64 in (67 mm) |

Environment

| | |
|--------------------|--------------------------------------|
| Enclosure Rating | NEMA 4X |
| Enclosure Material | Black plastic |
| Standards | UL 1449:ed. 4 CSA C22.2 No 8:1986 |
| Ambient Operating | 149 °F (65 °C) |

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

| | |
|---------------------|-------------------------------|
| Category | 08462 - SURGE PROTECTION SDSA |
| Discount Schedule | DE1B |
| GTIN | 00785901600022 |
| Package weight(Lbs) | 0.91 lb(US) (0.41 kg) |
| Returnability | Yes |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |

Approximate Dimensions

