



Main

Product or component type	Single Unit Manual Switch
Range of product	K

Complementary

Line Rated Current	20 A
Cable entry	0.75 NPT (bottom)
Motor power hp	2 hp at 115 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC 7.5 hp at 230 V AC 10 hp at 460 V AC 10 hp at 575 V AC
System Voltage	600 V AC 230 V DC
Poles description	3P
Control type	Toggle
Phase	3 phases
Local signalling	No indicator
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
AWG gauge	AWG 14...AWG 10 (copper)
Height	6.36 in
Width	3.95 in
Depth	4.35 in

Environment

Product certifications	UL listed file E58760 CCN NPXZ CSA LR26817 class 3218 04
------------------------	---

CE

NEMA degree of protection	NEMA 3R/7/9 cast aluminium standard size
---------------------------	--

Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901077725
Nbr. of units in pkg.	1
Package weight(Lbs)	3.5500000000000003
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------