

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Single Unit Manual Switch
Range of product	K

Complementary

Line Rated Current	30 A
Cable entry	0.75 NPT (bottom)
Motor power hp	3 hp at 460 V AC 2 hp at 230 V AC 2 hp at 115 V AC 3 hp at 575 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC
System Voltage	600 V AC 230 V DC
Poles description	2P
Control type	Toggle
Phase	1 phase
Local signalling	No indicator
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
AWG gauge	AWG 14...AWG 10 (copper)
Height	4.38 in
Width	3 in
Depth	4.25 in

Environment

Product certifications	CE CSA LR25490 class 3211 05
------------------------	---------------------------------

NEMA degree of protection	NEMA 4 die cast zinc alloy standard size
---------------------------	--

Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901554714
Nbr. of units in pkg.	1
Package weight(Lbs)	2.9500000000000002
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------