



### Main

Range of product	TeSys D TeSys K TeSys U TeSys GV2
Range	Lineryg
Product name	FT
Device short name	GV1G
Product or component type	Terminal block
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys - GV2 TeSys - U TeSys - D TeSys - K TeSys - LS1

### Complementary

[Ie] rated operational current	63 A
Mounting location	Top
IP degree of protection	IP20 according to IEC 60529
[Ui] rated insulation voltage	690 V according to IEC 60947-1
Connections - terminals	Screw clamp terminals 1 flexible AWG 4 Screw clamp terminals 1 solid AWG 4 Screw clamp terminals 1 cable(s) 1.5...10 mm <sup>2</sup> flexible with Screw clamp terminals 1 cable(s) 1.5...16 mm <sup>2</sup> flexible without Screw clamp terminals 1 cable(s) 1.5...25 mm <sup>2</sup> solid Screw clamp terminals 2 cable(s) 1.5...2 mm <sup>2</sup> flexible with Screw clamp terminals 2 cable(s) 1.5...6 mm <sup>2</sup> solid Screw clamp terminals 2 cable(s) 2.5...4 mm <sup>2</sup> flexible without
Tightening torque	1.7 N.m - on screw clamp terminals 2.2 N.m - on connector
Product weight	0.04 kg
Compatibility code	GV1G

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---