



Main

Range of product	TeSys U
Device short name	LUA1
Product or component type	Auxiliary contact

Complementary

Auxiliary contact composition	1 NO + 1 NC
Signalling function	Fault signalling Indicating rotary knob inready position
[Ue] rated operational voltage	<= 250 V AC <= 250 V DC
[Ui] rated insulation voltage	250 V conforming to CSA 250 V conforming to IEC 60947-5-1 250 V conforming to UL
[Ith] conventional free air thermal current	5 A
Minimum switching voltage	17 V
Minimum switching current	5 mA
Product weight	0.03 kg
Connections - terminals	Screw clamp terminals