



Main

Range	PowerLogic
Device short name	LVCT
Product or component type	Current transformer
Output voltage	0.333 V
Electrical connection	Cable 1.8 m 600 V
Product destination	BCPMCS
Range compatibility	BCPMSCA BCPMSCB BCPMSC E
Accessory / separate part category	Measurement accessory
Current transformer type	A type closed toroid
[In] rated current	200 A
Network frequency	50/60 Hz

Complementary

Measurement accuracy	+/- 0.5 % current range: 5...120 %
----------------------	------------------------------------

Environment

Climatic withstand	Relative humidity 95 %
Ambient air temperature for operation	-40...85 °C
Ambient air temperature for storage	-50...105 °C
Width	59 mm
Depth	18 mm
Height	25 mm diameter 59 mm external