



### Main

Range	ClimaSys
Product name	ClimaSys CC
Product or component type	Simple thermostat
Temperature setting range	0...60 °C
Information displayed	Temperature in °F

### Complementary

Input voltage	250 V
Sensor type	Bimetal
Contacts type and composition	NC
Contact resistance	< 10 mOhm
Service life in cycles	>= 100000 cycles
Maximum switching capacity	10 A 250 V AC resistive 15 A 120 V AC resistive 30 W DC 2 A 120...250 V AC inductive pf: 0.6
Electrical connection	4 terminals 2.5 mm <sup>2</sup>
Mounting mode	Clipped
Height	External : 68 mm
Width	External : 33 mm
Depth	External : 44 mm
Product weight	40 g
Mounting location	On mounting plate 35 mm DIN rail Spacial upright Cross rails
Ambient air temperature for operation	-20...80 °C
IP degree of protection	IP20
Hysteresis	7 %

Number of outputs	1 output(s) heating function
Material	PC
Colour	Light grey
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product certifications	UL

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------