



Main

Range	Spacial
Product name	Spacial CRNG
Device application	Multi-purpose
Product or component type	Compact enclosure
Enclosure nominal height	1000 mm
Enclosure nominal width	1000 mm
Enclosure nominal depth	300 mm
Installation accessory type	Wall-mounting
Device composition	Lock 1 Body 1 Door 2 Cable gland plate 2 bottom
Door type	Plain
Mounting plate description	Without mounting plate

Complementary

Variant particularity	Single piece body
Number of doors	2 front face
Door opening side	Reversible 120 °
Lock type	3 points lock, 5 mm double-bar
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Steel for body
Surface finish	Epoxy-polyester powder
Colour	Grey RAL 7035
Standards	IEC 62208
Product certifications	UL

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------