

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Modicon M171/M172
Product or component type	Display module
Supply	External source

Complementary

Display type	LCD display Colour touchscreen
Display resolution	320 x 240 pixels
Color	White
[Us] rated supply voltage	24 V AC/DC
Power consumption in W	3.2 VA 1.3 W
Analogue input type	NTC 10k type 2 temperature probe - 40...50 °C +/- 0.1 °C NTC 10k temperature probe at 21 °C +/- 0.5 °C
Product compatibility	Logic controller M171 Logic controller M172
Height	4.72 in (120 mm)
Width	3.39 in (86 mm)
Depth	0.98 in (25 mm)
Net Weight	0.75 lb(US) (0.34 kg)

Environment

Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Standards	EN 60950-1 EN 55024 EN 55032

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

UL 873
CSA C22.2 No 24

Product certifications	RCM EAC CE CTUVus
Ambient air temperature for operation	32...122 °F (0...50 °C)
Ambient air temperature for storage	-22...122 °F (-30...50 °C)

Ordering and shipping details

Category	22000 - Temporary Category for ITS Price Promotion
Discount Schedule	I
GTIN	00785901140856
Nbr. of units in pkg.	11
Package weight(Lbs)	11 lb(US) (4.99 kg)
Returnability	No

Packing Units

Package 1 Height	0.500 dm
Package 1 width	1.080 dm
Package 1 Length	1.550 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.