

# Product data sheet

## Characteristics

# TVS2HWA50X

Surge protection device, Surgelogic, HWA, 50kA, 208Y/120 VAC, 3 phase, 4 wire, NEMA 4X

Product availability : Stock - Normally stocked in distribution facility



### Main

Product	Surge protection device
Range	Surgelogic
Device Short Name	HWA

### Complementary

Surge Current	50 kA per phase
Voltage Rating	208Y/120 V AC
Number of Phases	3 phase
Wiring Configuration	4-wire
MCOV	150 V
Nominal Discharge Current	20 kA
SCCR	200 kA
Local Signalling	LED green normal operation Alarm
Height	9.4 in (238.76 mm)
Width	4.8 in (121.92 mm)
Depth	3.1 in (78.74 mm)
Cable length	33.6 in (853.44 mm)

### Environment

Enclosure Rating	NEMA 4X
Standards	UL 1449:ed. 4 type II UL 1283 NEC 285 CSA C22.2 No 8 UL 96A:ed. 12

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Operating	149 °F (65 °C)
-------------------	----------------

## Ordering and shipping details

Category	08466 - SURGE PROTECTION HWA
Discount Schedule	DE1B
GTIN	00785901293675
Package weight(Lbs)	5.08 lb(US) (2.30 kg)
Returnability	Yes
Country of origin	US

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.

## Contractual warranty

Warranty	18 months
----------	-----------