

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Meter Socket
Meter socket type	Ringed
Hub type	A ACP closing plate

Complementary

Meter socket rated current	200 A
Number of jaws	4 without jaw release
Bypass type	No bypass
Phase	1 phase
[Ue] rated operational voltage	600 V AC
Enclosure material	Steel
Box number	5R
Electrical connection	Lugs 0.5" hex
Service feed location	OH UG
Wiring configuration	3-wire
Height	15.00 in (381.00 mm)
Width	11.00 in (279.40 mm)
Depth	4.38 in (111.25 mm)

Environment

Product certifications	UL Listed
Enclosure Rating	NEMA 3R

Ordering and shipping details

Category	00039 - METER SOCKETS & HUBS
----------	------------------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	DE4
GTIN	00785901291138
Nbr. of units in pkg.	1
Package weight(Lbs)	13.12 lb(US) (5.95 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.40 in (13.716 cm)
Package 1 width	11.60 in (29.464 cm)
Package 1 Length	15.50 in (39.37 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	72
Package 2 Weight	945.00 lb(US) (428.644 kg)
Package 2 Height	40.00 in (101.6 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel (Metallic), which is known to the State of California to cause cancer, and Toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation

Contractual warranty

Warranty	18 months
----------	-----------