



## Main

Range of product	Altivar
Range compatibility	Altivar 312 Altivar 61 Altivar Lift Altivar 32 Altivar Machine ATV320 Altivar 312 Solar Altivar 212 Altivar 71 Altivar 61Q Altivar 71Q
Accessory / separate part category	Display and signalling accessories
Accessory / separate part type	Display terminal
Accessory / separate part destination	Variable speed drive
Product specific application	To control, adjust and configure the drive To save and download configurations To display the current values
IP degree of protection	IP54

## Complementary

Mounting location	On the door of an enclosure
Language	Italian English French Spanish German Chinese
Messages display capacity	8 lines
Pixel resolution	240 x 160
Net Weight	0.32 lb(US) (0.145 kg)

## Environment

Ambient air temperature for operation	5...122 °F (-15...50 °C)
---------------------------------------	--------------------------

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

Category	22135 - ATV61-71 ACCESSORIES
Discount Schedule	CP4C
GTIN	00785901684879
Nbr. of units in pkg.	1
Package weight(Lbs)	0.66 lb(US) (0.30 kg)
Returnability	Yes
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.39 in (8.6 cm)
Package 1 width	9.21 in (23.4 cm)
Package 1 Length	6.57 in (16.7 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------