

Product availability : Stock - Normally stocked in distribution facility



Main

| | |
|------------------------------------|--|
| Range of product | Harmony XVB Universal |
| Product or component type | Complete beacon |
| Beacon or indicator bank unit type | Base unit direct or tube fixing Illuminated unit |
| Signalling type | Steady |
| Mounting diameter | 2.76 in (70 mm) |
| Component name | XVBL |
| Material | Glass reinforced polyamide: base unit Polycarbonate: illuminated unit |
| Light source | Bulb not included, yellow |
| Bulb type | Incandescent with BA 15d base Protected LED |
| [Us] rated supply voltage | <= 250 V |
| Maximum power dissipation in W | 7 W |

Complementary

| | |
|--|--|
| Connections - terminals | Screw clamp terminals, <= 1 x 1.5 mm ² with cable end |
| [Ui] rated insulation voltage | 250 V IEC 60947-1 |
| Nominal voltage limit | 0.85...1.1 Un IEC 60947-5-1 |
| [Uimp] rated impulse withstand voltage | 4 kV IEC 60947-1 |
| CAD overall width | 2.76 in (70 mm) |
| CAD overall height | 5.47 in (139 mm) |
| CAD overall depth | 2.76 in (70 mm) |
| Terminals description ISO n°1 | (GND)GROUND (COM-1)PW |
| Net Weight | 0.57 lb(US) (0.26 kg) |

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

| | |
|---------------------------------------|---|
| Pollution degree | 2 |
| Product certifications | UL 508 CCC GOST CSA C22-2 No 14 |
| Standards | EN/IEC 60947-5-1 |
| Protective treatment | TC |
| Ambient air temperature for operation | -13...122 °F (-25...50 °C) LED -13...158 °F (-25...70 °C) incandescent |
| Ambient air temperature for storage | -40...158 °F (-40...70 °C) |
| Electrical shock protection class | Class I on support tube conforming to IEC 61140 Class II on base unit IEC 61140 |
| IP degree of protection | IP65 on fixing base XVBZ0. conforming to IEC 60529 IP66 on base unit conforming to IEC 60529 |
| NEMA degree of protection | NEMA 4X conforming to UL 508 (indoor) |

Ordering and shipping details

| | |
|-----------------------|-------------------------|
| Category | 22611 - XVB-STACKLIGHTS |
| Discount Schedule | XV |
| GTIN | 00785901844174 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.61 lb(US) (0.28 kg) |
| Returnability | Yes |
| Country of origin | CZ |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 3.15 in (8 cm) |
| Package 1 width | 3.15 in (8 cm) |
| Package 1 Length | 5.71 in (14.5 cm) |
| Unit Type of Package 2 | S03 |
| Number of Units in Package 2 | 18 |
| Package 2 Weight | 11.40 lb(US) (5.171 kg) |
| Package 2 Height | 11.81 in (30 cm) |
| Package 2 width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |

Offer Sustainability


| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Illuminated Beacon for BA 15d Bulb or LED

Dimensions



Illuminated Beacon

Wiring Diagram

