

Product data sheet

Characteristics

8903LG1200V02

Contactor, Type L, multipole lighting, electrically held, 30A, 12 pole, 600 V, 110/120 VAC 50/60 Hz coil, NEMA 1

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control Circuit	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush power in VA	180 VA 60 Hz 25 VA 50 Hz
Hold-in power consumption in VA	35 VA 60 Hz 35 VA 50 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	12P 12 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical connection	Screw-clamp terminals
Height	12.68 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.80 in (198 mm)
Net Weight	11.00 lb(US) (4.99 kg)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product certifications	UL Listed

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
GTIN	00785901851615
Nbr. of units in pkg.	1
Package weight(Lbs)	11.05 lb(US) (5.01 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	7.90 in (20.066 cm)
Package 1 width	8.40 in (21.336 cm)
Package 1 Length	13.20 in (33.528 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

