

## Product data sheet

### Characteristics

# 8903SVO11V02

Contactor, Type S, multipole lighting,  
mechanically held, 200A, 3 pole, 110/120VAC  
50/60Hz coil, open style

Product availability : Non-Stock - Not normally stocked in distribution facility



### Main

|         |                                      |
|---------|--------------------------------------|
| Product | Mechanically Held Lighting Contactor |
| Type    | S                                    |

### Complementary

|                         |                                  |
|-------------------------|----------------------------------|
| Control Circuit Voltage | 120 V AC 60 Hz<br>110 V AC 50 Hz |
| Current Rating          | 200 A                            |
| Number of Poles         | 3P                               |
| Control Units           | No control units                 |
| Pilot Light             | Without pilot light              |
| Auxiliary Contacts      | Without                          |
| Other Options           | None                             |
| Electrical connection   | Lugs                             |
| Height                  | 9.13 in (232 mm)                 |
| Depth                   | 6.73 in (171 mm)                 |
| Width                   | 5.98 in (152 mm)                 |

### Environment

|                        |                                      |
|------------------------|--------------------------------------|
| Enclosure Type         | Not rated (open device) surface none |
| Product certifications | UL Listed<br>CSA                     |

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Jun 11, 2021

### Ordering and shipping details

|                       |                                |
|-----------------------|--------------------------------|
| Category              | 21324 - 8903 S (NOT S*C) MECH. |
| Discount Schedule     | CP1                            |
| GTIN                  | 00785901102502                 |
| Nbr. of units in pkg. | 1                              |
| Package weight(Lbs)   | 23.33 lb(US) (10.58 kg)        |
| Returnability         | No                             |
| Country of origin     | MX                             |

### Packing Units

|                  |                      |
|------------------|----------------------|
| Package 1 Height | 9.70 in (24.638 cm)  |
| Package 1 width  | 13.70 in (34.798 cm) |
| Package 1 Length | 17.80 in (45.212 cm) |

### Offer Sustainability

|                           |                                                                                                                        |
|---------------------------|------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>             |
| REACH Regulation          | <a href="#">REACH Declaration</a>                                                                                      |
| EU RoHS Directive         | Not compliant                                                                                                          |
| China RoHS Regulation     | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information. |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|