

Product data sheet

Characteristics

JJA36250

Circuit breaker, PowerPacT J, I-Line, thermal magnetic, 250A, 3 pole, 25 kA, 600 VAC, phase ABC

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Circuit breaker
---------------------------	-----------------

Complementary

Number of Poles	3P
Breaking capacity code	J
Magnetic hold current	1250 A
Magnetic tripping current	2500 A
Electrical connection	I-Line connection line Lugs load
Tightening torque	230.12 lbf.in (26 N.m) 0.15...0.29 in ² (95...185 mm ²) AWG 3/0...350 kcmil)
Phase connection	ABC
Height	11.48 in (291.59 mm)
Width	4.48 in (113.79 mm)
Depth	5.87 in (149.10 mm)
Net Weight	5.29 lb(US) (2.4 kg)
Continuous current rating	80 %

Ordering and shipping details

Category	01117 - HG, HJ, JG, JJ I-LINE BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901689881
Nbr. of units in pkg.	1
Package weight(Lbs)	6.75 lb(US) (3.06 kg)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Jun 11, 2021

Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	6.20 in (15.748 cm)
Package 1 width	8.50 in (21.59 cm)
Package 1 Length	14.80 in (37.592 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------