

# Product data sheet

## Characteristics

# QO2175SB

Surge Breaker - QO - 22.5kA -120/240VAC -  
1P3W - T2

Product availability : Stock - Normally stocked in distribution facility



### Main

Product	Secondary surge arrester
Range	Surge Breaker QO

### Complementary

Surge Current	22.5 kA
Voltage Rating	120/240 V AC
Number of Phases	1 phase
Wiring Configuration	3-wire
MCOV	150 V 300 V
SCCR	22 kA
Local Signalling	1 LED green normal operation
Product destination	Load center QO
Height	93.98 mm (3.7 in)
Width	38.10 mm (1.5 in)
Depth	66.04 mm (2.6 in)

### Environment

Enclosure Rating	NEMA 2
Ambient Operating	149 °F (65 °C)

### Ordering and shipping details

Category	08461 - SURGE PROTECTION RESI
Discount Schedule	DE1B
GTIN	00785901210894

Package weight(Lbs)	0.29 kg (0.65 lb(US))
Returnability	Yes
Country of origin	MX

### Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.

### Contractual warranty

Warranty	18 months
----------	-----------