


## Rigid conduit/IMC fittings

### Reducers

Reducers - malleable iron/zinc plated




Cat. No.	Conduit Size (in.)	Dimensions (in.)		Std. Ctn.
		A	B	
RB 421	3/4-1/2	5/8	1 3/16	100
RB-432	1/2-3/4	1	1 3/16	100
RB-443	1-3/4	1 1/16	1 3/16	50



UL File No. E-23018.

### One-hole straps



One-hole straps – steel/zinc plated

Cat. No.	Screw Size	Conduit Size (in.)	Dimensions (in.)		Std. Ctn.
			A	B	
HS-100-SC	10	3/8	3/4	1 47/64	1,000
HS-101	1/4	1/2	1	1 15/16	500
HS-102	1/4	3/4	1	2 5/64	500
HS-103	1/4	1	1	2 13/32	250
HS-104	5/16	1 1/4	1	3 3/32	100
HS-105	3/8	1 1/2	1 3/16	3 13/32	100
HS-106	3/8	2	1 3/16	3 27/32	100
HS-107	7/16	2 1/2	1 1/4	5 1/16	25
HS-108	1/2	3	1 3/8	5 7/8	25
HS-109	1/2	3 1/2	1 3/8	6 1/4	10
HS-110	1/2	4	1 3/8	6 7/8	10

Available in one-hole and two-hole in stainless steel. Add SS suffix to catalog number for stainless steel.

### Two-hole straps


Two-hole straps – steel/zinc plated



Cat. No.	Screw Size	Conduit Size (in.)	Dimensions (in.)			Std. Ctn.
			A	B	C	
HS-901	8	1/2	3/4	2 7/16	3/16	1,200
HS-902	10	3/4	3/4	2 11/16	3/16	900
HS-903	1/4	1	3/4	3 7/16	3/16	600
HS-904	1/4	1 1/4	3/4	3 27/32	3/16	450
HS-905	1/4	1 1/2	3/4	4 1/16	3/16	50
HS-906	1/4	2	3/4	4 7/16	3/16	150
HS-907	1/4	2 1/2	1	5 1/8	1/4	150
HS-908	1/2	3	1	6 3/16	1/4	60
HS-909	1/4	3 1/2	1	7 3/16	1/4	60
HS-910	1/4	4	1	8 11/16	1/4	60

CSA Certified. Add SS suffix to catalog number for stainless steel.

### Reducing washers



Reducing washers – steel/zinc plated



Cat. No.	Conduit Size (in.)	Dimensions (in.)			Std. Ctn.
		A	B	C	
WA 110	1/2-3/8	1 3/16	1 1/16	2 7/32	500
WA-121	3/4-1/2	1 1/2	7/8	1 1/16	500
WA-131	1-1/2	1 3/4	7/8	1 5/16	500
WA-132	1-3/4	1 3/4	1 3/32	1 5/16	500
WA-141	1 1/4-1/2	2 3/16	7/8	1 11/16	200
WA-142	1 1/4-3/4	2 3/16	1 3/32	1 11/16	200
WA-143	1 1/4-1	2 3/16	1 23/64	1 11/16	200
WA-151	1 1/2-1/2	2 5/8	7/8	1 7/8	200
WA-152	1 1/2-3/4	2 5/8	1 3/32	1 7/8	200
WA-153	1 1/2-1	2 5/8	1 23/64	1 7/8	200
WA-154	1 1/2-1 1/4	2 5/8	1 23/64	1 7/8	200
WA-161	2-1/2	3 1/4	7/8	2 3/8	100
WA-162	2-3/4	3 1/4	1 3/32	2 3/8	100
WA-163	2-1	3 1/4	1 23/64	2 3/8	100
WA-164	2-1 1/4	3 1/4	1 23/32	2 3/8	100
WA-165	2-1 1/2	3 1/4	1 31/32	2 3/8	100
WA-171	2 1/2-1/2	3 1/4	7/8	2 7/8	100
WA-172	2 1/2-3/4	3 1/4	1 3/32	2 7/8	100
WA-173	2 1/2-1	3 1/4	1 23/64	2 7/8	100
WA-174	2 1/2-1 1/4	3 1/4	1 23/32	2 7/8	100
WA-175	2 1/2-1 1/2	3 1/4	1 31/32	2 7/8	100
WA-176	2 1/2-2	3 1/4	2 7/16	2 7/8	100
WA-181	3-1/2	4 1/2	7/8	3 1/2	100
WA-182	3-3/4	4 1/2	1 23/32	3 1/2	100
WA-183	3-1	4 1/2	1 23/64	3 1/2	100
WA-184	3-1 1/4	4 1/2	1 23/32	3 1/2	100
WA-185	3-1 1/2	4 1/2	1 31/32	3 1/2	100
WA-186	3-2	4 1/2	2 7/16	3 1/2	100
WA-187	3-2 1/2	4 1/2	2 5/16	3 1/2	100