

Filter Fan Replacement Filter Mats



086000-00

Filter Mats

- Synthetic fiber with progressive construction
- Temperature resistant to 212°F (100°C)
- Rating: G3 (coarse), G4 (coarse), and M5 (medium)
- Self-extinguishing class F1
- Moisture resistant to 100% RH
- Reusable; can be cleaned with mild soap or vacuum

Applications

- Replacement filter mats for Stego fans, grilles, and vents.

Features

- Filter media for enclosure fans
- Coarse or medium density

Replacement Filter Mats								
Part Number	Price	Dimensions HxW in (mm)	Use With Fan Part Number	Use With Grille or Vent Part Number	Filter Rating	Average Arrestance (Filtering Level)	Filter Density g/m ²	Pieces per Package
<u>086130-01</u>	\$9.00	11.10 X 11.10 [282 X 282]	<u>018600-02</u> <u>018600-04</u> <u>018610-00</u> <u>018610-02</u>	<u>118600-00</u> <u>018600-02</u> <u>018600-04</u> <u>018610-00</u> <u>018610-02</u>	G3 (coarse)	85%	350 g/m ²	3
<u>086330-00</u>	\$10.25	3.31 x 3.31 [84 x 84]	<u>018700-30</u> <u>018701-30</u> <u>018702-30</u> <u>018703-30</u> <u>018709-30</u> <u>018800-40</u> <u>018809-40</u>	<u>118800-30</u>		84%	200 g/m ²	5
<u>086340-00</u>	\$13.75	4.64 x 4.64 [118 x 118]	<u>018010-01</u> <u>018010-02</u> <u>018210-02</u> <u>018210-04</u> <u>018710-30</u> <u>018711-30</u> <u>018712-30</u> <u>018713-30</u> <u>018719-30</u> <u>018810-40</u> <u>018819-40</u>	<u>118010-00</u> <u>118210-00</u> <u>118810-30</u>				
<u>086350-00</u>	\$18.00	6.61 x 6.61 [168 x 168]	<u>018020-01</u> <u>018020-02</u> <u>018040-01</u> <u>018720-30</u> <u>018721-30</u> <u>018722-30</u> <u>018723-30</u> <u>018729-30</u> <u>018820-40</u> <u>018829-40</u>	<u>118020-00</u> <u>118820-30</u>				
<u>086360-00</u>	\$23.50	8.46 x 8.46 [215 x 215]	<u>018730-30</u> <u>018830-40</u> <u>018839-40</u>	<u>118830-30</u>				
<u>086370-00</u>	\$31.00	11.14 x 11.14 [283 x 283]	<u>018740-30</u> <u>018749-30</u> <u>018840-40</u> <u>018849-40</u>	<u>118840-30</u>				

Note: Dimensions in inches [millimeters].

Filter Fan Replacement Filter Mats



Replacement Filter Mats								
Part Number	Price	Dimensions HxW in (mm)	Use With Fan Part Number	Use With Grille or Vent Part Number	Filter Rating	Average Arrestance (Filtering Level)	Filter Density g/m2	Pieces per Package
086000-00	\$7.50	3.50 x 3.50 [89 x 89]	018700-30 018701-30 018702-30 018703-30 018709-30 018800-40 018809-40	118800-30	G4 (coarse)	94%	350 g/m2	3
086010-00	\$9.25	4.65 x 4.65 [118 x 118]	018000-01 018000-02	118000-00				
086020-00	\$11.50	6.61 x 6.61 [168 x 168]	018010-01 018010-02 018210-02 018210-04 018710-30 018711-30 018712-30 018713-30 018719-30 018810-40 018819-40	118010-00 118210-00 118810-30				
086030-00	\$8.75	3.50 x 3.50 [89 x 89]	018020-01 018020-02 018040-01 018720-30 018721-30 018722-30 018723-30 018729-30 018829-40 018829-40	118020-00 118820-30				
086040-00	\$11.25	4.65 x 4.65 [118 x 118]	018730-30 018739-30 018830-40 018839-40	118830-30				
086050-00	\$16.50	6.61 x 6.61 [168 x 168]	018030-01 018030-03 018050-01	118030-00				
086080-00	\$28.50	9.72 x 9.72 [247 x 247]	018740-30 018749-30 018840-40 018849-40	118840-30				
086090-00	\$35.00	9.72 x 9.72 [247 x 247]	018700-30 018701-30 018702-30 018703-30 018709-30 018800-40 018809-40	118800-30	M5 (medium))	98%	350 g/m2	3
086270-00	\$8.75	3.31 x 3.31 [84 x 84]	018000-01 018000-02	118000-00	M5 (medium))	98%		

Note: Dimensions in inches [millimeters].

Filter Fan Replacement Filter Mats



Replacement Filter Mats								
Part Number	Price	Dimensions HxW in (mm)	Use With Fan Part Number	Use With Grille or Vent Part Number	Filter Rating	Average Arrestance (Filtering Level)	Filter Density g/m2	Pieces per Package
<u>086280-00</u>	\$16.00	8.46 x 8.46 [215 x 215]	<u>018010-01</u> <u>018010-02</u> <u>018210-02</u> <u>018210-04</u> <u>018710-30</u> <u>018711-30</u> <u>018712-30</u> <u>018713-30</u> <u>018719-30</u> <u>018810-40</u> <u>018819-40</u>	<u>118010-00</u> <u>118210-00</u> <u>118810-30</u>	M5 (medium))	98%	350 g/m2	3
<u>086290-00</u>	\$22.00	11.14 x 11.14 [283 x 283]	<u>018020-01</u> <u>018020-02</u> <u>018040-01</u> <u>018720-30</u> <u>018721-30</u> <u>018722-30</u> <u>018723-30</u> <u>018729-30</u> <u>018820-40</u> <u>018829-40</u>	<u>118020-00</u> <u>118820-30</u>				
<u>086300-00</u>	\$8.75	3.31 x 3.31 [84 x 84]	<u>018740-30</u> <u>018739-30</u> <u>018830-40</u> <u>018839-40</u>	<u>118840-30</u>	M5 (medium))	98%	360 g/m2	3
<u>086310-00</u>	\$16.00	8.46 x 8.46 [215 x 215]	<u>018030-01</u> <u>018030-03</u> <u>018050-01</u>	<u>118030-00</u>				
<u>086320-00</u>	\$22.00	11.14 x 11.14 [283 x 283]	<u>018740-30</u> <u>018749-30</u> <u>018840-40</u> <u>018849-40</u>	<u>118840-30</u>				

Note: Dimensions in inches [millimeters].