


Stego, Inc.

95 Chastain Road NW

Suite 200

Kennesaw, GA 30144, USA

Toll-Free: (888) 783-4611 • **Phone:** (770) 984-0858

Email: info@stegousa.com • **Website:** www.stego-usa.com
Part # 01177.0-00, Dual Thermostat

[Specifications](#) | [Technical Data](#)
Specifications

Setting Range - NC	-10 to 50 °C
Setting Range - NC	-10 to 50 °C
Agency Approvals	CSA, VDE

Technical Data

Sensor Element	Thermostatic bi-metal
Switching Difference (Hysteresis)	7 °C ± 4 °C
Maximum Tolerance	± 4 K
Switching Capacity (Max. Load)	NC: 10 A resistive/2 A inductive at 250 VAC NO: 5 A resistive/2 A inductive at 250 VAC DC 30W
Minimum Load	20 mA (all voltages)
EMI/EMC Compliance	EN 55014-1-2, EN 61000-3-2, EN 61000-3-3
Connection	4-pole terminal for AWG 14 max. (2.5 mm ²)
Mounting	Clip for 35 mm DIN rail (EN 60 715)

Dimensions (H x W x D)	2.6 x 2.0 x 1.8 inches (67 x 50 x 46 mm)
-------------------------------	--

Housing	Plastic, UL 94V-0, light gray
----------------	-------------------------------

Weight	3.2 oz (90 g)
---------------	---------------

Operating/Storage Temperature	-49 to 158 °F (-45 to 70 °C)
--------------------------------------	------------------------------

Protection Type	IP20
------------------------	------