



**Alternate Catalog No. 703 1/2 EG**  
**Catalog No. 7031/2EG**

**Description: UNIV CLP 16GA SZ 1/2IN OD.706IN EG**

**UPC No 616013143612**

**Home > Wire & Cable Management > Superstrut > Hose or pipe clamps**

Clamp, Universal, 16 Gauge, Size 1/2 Inch, Pipe Outer Diameter .706 Inches - .840 Inches, Electro-Galvanized Steel, For use with Rigid or IMC Conduit, Pipe and Electrical Metal Tubing

**Descriptors**

Category	Hose or pipe clamps
Special Features	Bolt head is combination slot and hex head for flexibility of attachment
Application	Superstrut Pipe Straps are designed to be twist inserted anywhere along the slot side of the channel.

**Specifications**

Material	Steel
Finish	SilverGalv/Electro-Galvanized
Number Of Holes	0

**Classifications**

Brand Name	Superstrut
------------	------------

**Dimensions**

Maximum Clamp Diameter	0.840 in
Minimum Clamp Diameter	0.706 in

**Compliance and Certifications**

TSCA	TSCA Section 6(h) Compliant
------	-----------------------------