

KCAP High Endurance Capacitors

Three-Phase Dry Type Individual Caps

Individual Caps	Part Number	Voltage	kVar	Dimensions (in.) Height x Diameter	
	28565	480	10	8.48 x 3.32	
	28566	480	15	8.48 x 3.32	
	28541	480	20	11.43 x 3.32	
	28567	600	5	8.30 x 2.53	
	28568	600	10	8.30 x 3.32	
	28569	600	15	11.31 x 3.31	
	28570	600	20	14.25 x 3.32	

Three-Phase Oil Filled Individual Caps

Individual Caps	Part Number	Voltage	kVar	Dimensions (in.) Height x Diameter	
	KCAP5B6B	240	5	7.50 x 3.33	
	KCAP10B6B	240	10	10.50 x 3.33	
	27605	480	3	7.46 x 3.00	
	27606	480	5	7.46 x 3.00	
	28503	480	6	8.24 x 3.35	

Single-Phase Oil Filled Individual Caps

Caps	Part Number	Voltage	Dimensions (in.) Height x Diameter	
	28356	330	3.30 x 1.75	
	28654	330	3.30 x 1.75	

Mounting Brackets	Part Number	# of Cells	
	KCAPBKT1B	1	
	KCAPBKT2B	2	
	KCAPBKT4B	4	