

KDR Optimized Line Reactors

Part Number	NEC Motor HP	Open		UL Type 1 Enclosed		UL Type 3R Enclosed	
		Weight		Part Number *		Part Number *	
KDRULA55L	0.5	4		KDRULA55LE01		KDRULA55LE3R	
KDRULA56L	0.75	4		KDRULA56LE01		KDRULA56LE3R	
KDRULA50L	1	4		KDRULA50LE01		KDRULA50LE3R	
KDRULA51L	1.5	4		KDRULA51LE01		KDRULA51LE3R	
KDRULA46L	2	4		KDRULA46LE01		KDRULA46LE3R	
KDRULA52L	3	4		KDRULA52LE01		KDRULA52LE3R	
KDRULA47L	5	4		KDRULA47LE01		KDRULA47LE3R	
KDRULA48L	7.5	4		KDRULA48LE01		KDRULA48LE3R	
KDRULA49L	10	5		KDRULA49LE01		KDRULA49LE3R	
KDRULB45L	15	8		KDRULB45LE01		KDRULB45LE3R	
KDRULB44L	20	8		KDRULB44LE01		KDRULB44LE3R	
KDRULB43L	25	8		KDRULB43LE01		KDRULB43LE3R	
KDRULD42L	30	12		KDRULD42LE01		KDRULD42LE3R	
KDRULC43L	40	15		KDRULC43LE01		KDRULC43LE3R	
KDRULC44L	50	15		KDRULC44LE01		KDRULC44LE3R	
KDRULF46L	60	30		KDRULF46LE01		KDRULF46LE3R	
KDRULF47L	75	30		KDRULF47LE01		KDRULF47LE3R	
KDRULF45L	100	33		KDRULF45LE01		KDRULF45LE3R	
KDRULH43L	125	48		KDRULH43LE01		KDRULH43LE3R	
KDRULH44L	150	51		KDRULH44LE01		KDRULH44LE3R	
KDRULI42L	200	56		KDRULI42LE01		KDRULI42LE3R	
KDRULG47L	250	74		KDRULG47LE01		KDRULG47LE3R	
KDRULG45L	300	74		KDRULG45LE01		KDRULG45LE3R	
KDRULJ45L	350	79		KDRULJ45LE01		KDRULJ45LE3R	
KDRULJ43L	400	79		KDRULJ43LE01		KDRULJ43LE3R	
KDRULJ44L	450	79		KDRULJ44LE01		KDRULJ44LE3R	
KDRULL45L	500	125		KDRULL45LE01		KDRULL45LE3R	
KDRULL42L	600	165		KDRULL42LE01		KDRULL42LE3R	
KDRULL43L	700	288		KDRULL43LE01			
KDRULS41L	800	293		KDRULS41LE01			
KDRULX41L	900	280		KDRULX41LE01			
KDRULX42L	1000	314		KDRULX42LE01			
KDRULX43L	1100	340		KDRULX43LE01			
KDRULX44L	1250	350		KDRULX44LE01			
KDRULY41L	1500	525		KDRULY41LE01			

575/600 Volt Low-Z

