

KDR Optimized Line Reactors

690 Volt High-Z	Part Number	NEC Motor HP	NEC Motor	Watts Loss	Standard Terms	Dimensions (in.) Height x Width x Depth	Open Weight	NEMA 1 Enclosed Part Number *
	KDRA55HV	0.5	0.9	9	QD	4.00 x 4.18 x 3.75	4	KDRA55HC1V
	KDRA52HV	0.75	1.3	13	QD	4.00 x 4.18 x 3.75	4	KDRA52HC1V
	KDRA50HV	1	1.7	17	QD	4.00 x 4.18 x 3.75	4	KDRA50HC1V
	KDRA51HV	1.5	2.4	26	QD	4.00 x 4.18 x 3.75	4	KDRA51HC1V
	KDRA43HV	2	2.7	24	QD	4.00 x 4.18 x 3.75	4	KDRA43HC1V
	KDRA44HV	3	3.9	35	QD	4.00 x 4.18 x 3.75	4	KDRA44HC1V
	KDRA45HV	5	6.1	48	QD	4.00 x 4.18 x 3.75	4	KDRA45HC1V
	KDRB42HV	7.5	9	61	QD	5.00 x 6.00 x 4.00	8	KDRB42HC2V
	KDRB43HV	10	11	71	QD	5.00 x 6.00 x 4.00	8	KDRB43HC2V
	KDRB44HV	15	17	73	RL	5.00 x 6.00 x 4.50	8	KDRB44HC2V
	KDRD41HV	20	22	106	RL	5.75 x 7.20 x 4.50	12	KDRD41HC2V
	KDRC43HV	25	27	107	RL	5.75 x 7.20 x 5.00	15	KDRC43HC2V
	KDRE42HV	30	32	140	RL	5.75 x 7.20 x 5.12	16	KDRE42HC3V
	KDRF44HV	40	41	172	RL	7.00 x 9.00 x 6.00	30	KDRF44HC3V
	KDRF45HV	50	52	166	RL	7.00 x 9.00 x 6.00	30	KDRF45HC3V
	KDRH43HV	60	62	205	RL	8.50 x 11.00 x 6.50	45	KDRH43HC4V
	KDRH42HV	75	77	251	RL	8.50 x 11.00 x 6.50	45	KDRH42HC4V
	KDRI41HV	100	99	268	CB	9.00 x 11.00 x 7.00	50	KDRI41HC4V
	KDRG44HV	125	125	381	CB	9.00 x 11.00 x 7.50	65	KDRG44HC4V
	KDRG45HV	150	144	406	CB	9.00 x 11.00 x 8.00	65	KDRG45HC4V
	KDRJ41HV	200	192	466	CB	9.00 x 11.00 x 9.00	70	KDRJ41HC5V
	KDRL46HV	250	242	472	CB	11.38 x 15.00 x 11.00	110	KDRL46HC5V
	KDRL47HV	300	289	490	CB	11.38 x 15.00 x 11.00	110	KDRL47HC5V
	KDRL48HV	350	336	539	CB	11.38 x 15.00 x 11.00	110	KDRL48HC5V
	KDRL49HV	400	382	603	CB	11.38 x 15.00 x 11.00	110	KDRL49HC5V
	KDRS47HV	450	412	521	CB	11.38 x 15.00 x 13.00	165	KDRS47HC5V
	KDRS46HV	500	472	661	CB	11.38 x 15.00 x 13.00	165	KDRS46HC5V
	KDRS49HV	600	576	1194	CB	11.38 x 15.00 x 13.00	175	KDRS49HC5V
	KDRX45HV	700	672	1393	CB	18.50 x 18.25 x 12.50	200	KDRX45HC7V
	KDRX44HV	800	768	1592	CB	18.50 x 18.25 x 12.50	280	KDRX44HC7V
	KDRX41HV	900	864	1791	CB	18.50 x 18.25 x 12.50	290	KDRX41HC7V
	KDRX42HV	1000	960	1990	CB	18.50 x 18.25 x 12.50	375	KDRX42HC7V
	KDRX43HV	1100	1056	2189	CB	18.50 x 18.25 x 12.50	450	KDRX43HC7V
	KDRY41HV	1250	1200	2488	CB	20.00 x 21.00 x 16.00	475	KDRY41HC7V
	KDRY42HV	1500	1440	2985	CB	20.00 x 21.00 x 16.00	575	KDRY42HC7V

Part Numbering System

