



NOTE: FOR TERMINAL TORQUE SEE IOM MANUAL.

MSD PART NUMBER	HP	VOLTAGE	CURRENT	WEIGHT	PRESSURE TERMINAL WIRE RANGE
MSD0480A300	400	480V	480 AMPS	630LBS	(2) 600MCM-4AWG

CUSTOMER IS RESPONSIBLE FOR INSTALLATION TO MEET ALL NATIONAL AND LOCAL ELECTRICAL CODES.

NO	REVISION	DATE	BY	TOLERANCES (EXCEPT AS NOTED)	SCALE	DATE	APRVD.	DWG. No.	SHEET	OF
B	3696 ADD DISCHARGE LABEL	8/1/16	DSW	DECIMAL .XX +/- .25 .XXX +/- .10	1/8	7/14/2015		W132 N10611 Grant Drive Germantown, WI 53022	1	1
A	AS BUILT	7/14/15	DSW	FRACTIONAL +/- 1/16 ANGULAR +/- 1°				MSD0480A300 MotorShield Sinewave Filter 480 AMPS, 480/3/60, Type 1/3R.	1	1
NO								106075DG	1	1