





CUSTOMER CONNECTIONS

75 HP AND BELOW : USE MINIMUM 60°C COPPER WIRE
ABOVE 75 HP : USE MINIMUM 75°C COPPER WIRE

FACTORY POWER CONNECTIONS

CONTROL CONNECTIONS



Material(s) Shall be RoHS Compliant

THE INFORMATION AND DESIGNS CONTAINED IN THIS DRAWING ARE CONFIDENTIAL AND THE PROPERTY OF ALLIED MOTION TECHNOLOGIES INC. AND ITS SUBSIDIARIES. NEITHER THIS DESIGN NOR ANY INFORMATION CONTAINED IN THIS DRAWING MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE EXPRESS WRITTEN CONSENT OF ALLIED MOTION TECHNOLOGIES INC. AND ITS SUBSIDIARIES.				TOLERANCES EXCEPT AS NOTED		 W132 N10611 Grant Drive Germantown, WI 53022 © TCL, 2021			
				XX ± NA	FACTUAL	HarmonicGuard Low Capacitance			
C	6382 Update T/S Connections	08/16/23	JRN	± NA	FACTUAL	480V Contactor/PQconnect			
B	6024 Schematic Update	8/23/22	JTL	± NA	FACTUAL				
NO	REVISION	DATE	RY	± NA	FACTUAL				
				JRN BY	DATE	SCALE	SIZE	DWG. NO.	
				DSW	4/6/19	NA	C	30586-PQ	
								SHEET 1 OF 1	