

LED

25,000 Hours average rated life, 120Volts

Applications:

Suitable for outdoor fixtures. Also perfect for applications with hard to reach areas, vibration, and frequent starts.

Accent and decorative lighting including:

- + Chandeliers
- + Ceiling Fans
- + Decorative
- + Indoor Fixtures
- + Outdoor Fixtures
- + Wall Sconces



Light output equivalency:

7w = 60w

Features and Benefits

- Long Life: 25,000 hours – no more bulb replacements.
- Excellent white color consistency from bulb to bulb.
- UL approved for dry and damp locations.

** Three or more lamps per dimming circuit is recommended for optimal dimming.*

7W Torpedo B13

Catalog Number

Notes

Type


Specifications (at full brightness)

Input Line Voltage:	120VAC
Input Line Frequency	60HZ
Lamp Life (Rated)	25,000 hrs
Minimum Starting Temp	-30°C
Maximum Operating Temp.....	40°C
UL/cUL Listed	Yes
CRI	82

Warranties and Certifications:	Item #	Description	Voltage	Wattage	Wattage Equivalent	M.O.L. (inches)	Diameter (inches)	Lumens	LPW	CCT	CRI
3 YEAR WARRANTY 	LED7E26B1324KF	LED 7W NON DIMMABLE BLUNT TIP - 2400K	120	7.0	60W	4.54	1.61	425	60.7	2400K	82
	LED7E26B1327KF	LED 7W NON DIMMABLE BLUNT TIP - 2700K	120	7.0	60W	4.54	1.61	500	71.4	2700K	82
	LED7E26B13D24KF	LED 7W DIMMABLE BLUNT TIP - 2400K	120	7.0	60W	4.54	1.61	425	60.7	2400K	82
	LED7E26B13D27KF	LED 7W DIMMABLE BLUNT TIP - 2700K	120	7.0	60W	4.54	1.61	500	71.4	2700K	82