



Item Number

Item Description

Voltage

Lamp Watts

Wattage Equivalent

Lumens

Lumens Per Watt

CCT

CRI

Case Quantity

**15,000 HOUR OMNIDIRECTIONAL A-LAMPS (REPLACES 40W)**

**6W NON-DIMMABLE A19 - OMNIDIRECTIONAL (REPLACES 40W)**



L6A19N1527K	Non-Dimmable 6W Omnidirectional A19 - 2700K	120	6	40W	480	80.0	2700K	80	12
L6A19N1530K	Non-Dimmable 6W Omnidirectional A19 - 3000K	120	6	40W	480	80.0	3000K	80	12
L6A19N1541K	Non-Dimmable 6W Omnidirectional A19 - 4100K	120	6	40W	500	83.3	4100K	80	12
L6A19N1550K	Non-Dimmable 6W Omnidirectional A19 - 5000K	120	6	40W	525	87.5	5000K	80	12

**25,000 HOUR ELITE HI CRI A-LAMPS (REPLACES 60W)**


**11W HI CRI DIMMABLE A19 - OMNIDIRECTIONAL (REPLACES 60W)**



LED11A19D0D27K95	Dimmable 11W Hi CRI OmniDirectional A19 - 2700K	120	11	60W	800	72.7	2700K	90	12
LED11A19D0D30K95	Dimmable 11W Hi CRI OmniDirectional A19 - 3000K	120	11	60W	825	75.0	3000K	90	12

**25,000 HOUR ELITE HI CRI GU24 BASED A-LAMPS (REPLACES 60W)**


**11W GU24 BASED HI CRI DIMMABLE A19 - OMNIDIRECTIONAL (REPLACES 60W)**



LED11A19GUD0D27K95	Dimmable 11W Hi CRI GU24 OmniDirectional A19 - 2700K	120	11	60W	800	72.7	2700K	90	12
LED11A19GUD0D30K95	Dimmable 11W Hi CRI GU24 OmniDirectional A19 - 3000K	120	11	60W	800	72.7	3000K	90	12

**25,000 HOUR ELITE GU24 BASED A-LAMPS (REPLACES 60W)**

**10W GU24 BASED DIMMABLE A19 - OMNIDIRECTIONAL (REPLACES 60W)**



LED10A19GUD0D27K	Dimmable 10W GU24 OmniDirectional A19 - 2700K	120	10	60W	800	80.0	2700K	80	12
LED10A19GUD0D30K	Dimmable 10W GU24 OmniDirectional A19 - 3000K	120	10	60W	825	82.5	3000K	80	12
LED10A19GUD0D41K	Dimmable 10W GU24 OmniDirectional A19 - 4100K	120	10	60W	850	85.0	4100K	80	12

**25,000 HOUR ELITE 60W WET LOCATION A-LAMPS (REPLACES 60W)**

**9.5W WET LOCATION A19 OMNIDIRECTIONAL A-LAMP (REPLACES 60W)**



LED10A19D0D27KW	Dimmable 9.5W Omnidirectional Wet Location A19 - 2700K	120	9.5	60W	800	84.2	2700K	80	12
LED10A19D0D30KW	Dimmable 9.5W Omnidirectional Wet Location A19 - 3000K	120	9.5	60W	825	86.8	3000K	80	12
LED10A19D0D41KW	Dimmable 9.5W Omnidirectional Wet Location A19 - 4100K	120	9.5	60W	850	89.5	4100K	80	12

Item Number

Item Description

Voltage

Wattage/Lumens

Wattage/LPW

16W

8W

4W

16W

8W

4W

CCT

CRI

Case Quantity

**25,000 HOUR ELITE 100W LED THREE WAY A-LAMPS (REPLACES 100W/60W/40W)**

**16W/8W/4W A21 - THREE WAY A-LAMPS (REPLACES 100W/60W/40W)**



LED16A21D3WAY27K	16W/8W/4W A21 - 2700K	120	1600	900	500	100.0	112.5	125.0	2700K	80	12
LED16A21D3WAY30K	16W/8W/4W A21 - 3000K	120	1650	950	550	103.1	118.8	110.0	3000K	80	12
LED16A21D3WAY41K	16W/8W/4W A21 - 4100K	120	1700	1000	600	106.3	125.0	150.0	4100K	80	12
LED16A21D3WAY50K	16W/8W/4W A21 - 5000K	120	1750	1050	650	109.4	131.3	162.5	5000K	80	12

10



5 YEAR WARRANTY  
25,000 HOUR LAMPS

3 YEAR WARRANTY  
15,000 HOUR LAMPS

1 YEAR WARRANTY  
10,000 HOUR LAMPS