

# TECO Westinghouse

ISSUED <b>September 25, 2017</b>	<b>PERFORMANCE DATA</b> <b>3-PHASE INDUCTION MOTOR</b>	ENCLOSURE <b>WP1</b>
TYPE <b>AMRCNH</b>		CATALOG# <b>VHP5004</b>

### NAMEPLATE INFORMATION

OUTPUT		POLE	FRAME SIZE	VOLTAGE	HZ	RATED AMBIENT	INS. CLASS	NEMA DESIGN	TIME RATING	SERVICE FACTOR
HP	KW									
<b>500</b>	<b>373</b>	<b>4</b>	<b>5009.0</b>	<b>230/460</b>	<b>60</b>	<b>40°C</b>	<b>F</b>	<b>B</b>	<b>CONT.</b>	<b>1.15</b>

### TYPICAL PERFORMANCE

FULL LOAD RPM	EFFICIENCY				POWER FACTOR			MAXIMUM POWER FACTOR CORRECTION
	FULL LOAD		3/4 LOAD	1/2 LOAD	F. L.	3/4 LOAD	1/2 LOAD	
	MIN. %	NOM. %	%	%	%	%	%	
<b>1779</b>	<b>95.4</b>	<b>96.0</b>	<b>96.0</b>	<b>95.5</b>	<b>88.8</b>	<b>88.3</b>	<b>84.3</b>	<b>113.4 KVAR</b>

### CURRENTS

NO LOAD			FULL LOAD			LOCKED ROTOR			NEMA KVA CODE LETTER
AT 208 VOLT	AT 230 VOLT	AT 460 VOLT	AT 208 VOLT	AT 230 VOLT	AT 460 VOLT	AT 208 VOLT	AT 230 VOLT	AT 460 VOLT	
<b>0.0</b>	<b>0.0</b>	<b>142</b>	<b>1212</b>	<b>0</b>	<b>548</b>	<b>8744</b>	<b>0</b>	<b>3954</b>	

### TORQUE

### INERTIA

### ACCEL TIME

FULL LOAD lb-ft	LOCKED ROTOR %FLT	PULL UP %FLT	BREAK DOWN %FLT	ROTOR WR <sup>2</sup> lb-ft <sup>2</sup>	NEMA LOAD WK <sup>2</sup> lb-ft <sup>2</sup>	MAX ALLOWABLE WK <sup>2</sup> lb-ft <sup>2</sup>	NEMA LOAD WK <sup>2</sup> Sec	MAX ALLOWABLE WK <sup>2</sup> Sec
<b>1477</b>	<b>110</b>	<b>99</b>	<b>200</b>	<b>158</b>	<b>1880</b>	<b>2256</b>	<b>5.20</b>	<b>6.16</b>

SAFE STALL TIME IN SECONDS

ALLOWABLE STARTS PER HOUR

SOUND PRESSURE LEVEL @ 3 FT dB(A)

COLD	HOT	COLD	HOT	
<b>18.2</b>	<b>15.2</b>	<b>2</b>	<b>1</b>	<b>86</b>

APPROVED:	<b>M. PRATER</b>	DRAWING NO.	<b>31057VHP5004</b>	REVISION <b>0</b>
-----------	------------------	-------------	---------------------	-------------------