

# TECO Westinghouse

|                                |                                |                                     |
|--------------------------------|--------------------------------|-------------------------------------|
| ISSUED<br><b>July 12, 2018</b> | <b>PERFORMANCE DATA</b>        | ENCLOSURE<br><b>EXPLOSION PROOF</b> |
| TYPE<br><b>AEUHXG</b>          | <b>3-PHASE INDUCTION MOTOR</b> | CATALOG#<br><b>XPV0404C</b>         |

### NAMEPLATE INFORMATION

| OUTPUT    |             | POLE     | FRAME SIZE   | VOLTAGE        | HZ        | RATED AMBIENT | INS. CLASS | NEMA DESIGN | TIME RATING  | SERVICE FACTOR |
|-----------|-------------|----------|--------------|----------------|-----------|---------------|------------|-------------|--------------|----------------|
| HP        | KW          |          |              |                |           |               |            |             |              |                |
| <b>40</b> | <b>29.8</b> | <b>4</b> | <b>324TC</b> | <b>230/460</b> | <b>60</b> | <b>40°C</b>   | <b>F</b>   | <b>B</b>    | <b>CONT.</b> | <b>1.15</b>    |

### TYPICAL PERFORMANCE

| FULL LOAD RPM | EFFICIENCY |             |           |           | POWER FACTOR |           |           | MAXIMUM POWER FACTOR CORRECTION |
|---------------|------------|-------------|-----------|-----------|--------------|-----------|-----------|---------------------------------|
|               | FULL LOAD  |             | 3/4 LOAD  | 1/2 LOAD  | F. L.        | 3/4 LOAD  | 1/2 LOAD  |                                 |
|               | MIN. %     | NOM. %      |           |           |              |           |           |                                 |
| <b>1770</b>   | <b>93</b>  | <b>94.1</b> | <b>94</b> | <b>94</b> | <b>85.5</b>  | <b>84</b> | <b>79</b> | <b>8.8 KVAR</b>                 |

### CURRENTS

| NO LOAD      |              |              | FULL LOAD     |              |              | LOCKED ROTOR  |               |               | NEMA KVA CODE LETTER |
|--------------|--------------|--------------|---------------|--------------|--------------|---------------|---------------|---------------|----------------------|
| AT           | AT           | AT           | AT            | AT           | AT           | AT            | AT            | AT            |                      |
| 208 VOLT     | 230 VOLT     | 460 VOLT     | 208 VOLT      | 230 VOLT     | 460 VOLT     | 208 VOLT      | 230 VOLT      | 460 VOLT      |                      |
| <b>24.55</b> | <b>22.20</b> | <b>11.10</b> | <b>103.06</b> | <b>93.20</b> | <b>46.60</b> | <b>641.35</b> | <b>580.00</b> | <b>290.00</b> | <b>G</b>             |

### TORQUE

### INERTIA

### ACCEL TIME

| FULL LOAD lb-ft | LOCKED ROTOR %FLT | PULL UP %FLT | BREAK DOWN %FLT | ROTOR WR <sup>2</sup> lb-ft <sup>2</sup> | NEMA LOAD WK <sup>2</sup> lb-ft <sup>2</sup> | MAX ALLOWABLE WK <sup>2</sup> lb-ft <sup>2</sup> | NEMA LOAD WK <sup>2</sup> Sec | MAX ALLOWABLE WK <sup>2</sup> Sec |
|-----------------|-------------------|--------------|-----------------|--|--|--|-------------------------------|-----------------------------------|
| <b>118.7</b>    | <b>225</b>        | <b>180</b>   | <b>215</b>      | <b>8.624</b>                             | <b>189</b>                                   | <b>309.00</b>                                    | <b>4.80</b>                   | <b>7.72</b>                       |

SAFE STALL TIME IN SECONDS

ALLOWABLE STARTS PER HOUR

SOUND PRESSURE LEVEL @ 3 FT dB(A)

| COLD      |           | HOT      |          | 70 |
|-----------|-----------|----------|----------|----|
| <b>17</b> | <b>12</b> | <b>2</b> | <b>1</b> |    |

APPROVED:

**M. PRATER**

DRAWING NO.

**31057XPV0404C**

REVISION **0**