

11

10

9

8

7

6

5

4

3

2

1

POLE	HP	kW	Hz	VOLT	r/min(RPM)	INS	RATING	DIMENSION IN	APPROX WEIGHT	BEARINGS
6	150	111.9	60	460	1200	F	CONT.	INCH		DE: 6320 NDE: 6316

49.52

23.52

17.15

8.50

PRIMARY T-BOX (2~NPT3")

USABLE SHAFT LENGTH

8.00

6.93

8~ $\phi$ 0.81 HOLES

17.02

13.52

6.70

5.51

16.50

6.70

7.50

20.00

23.25

24.00

24.00

4.35

23.55

11.00  $+0.06$

1.83

GROUNDING TERMINAL

4.35

17.90

9.00

9.00

22.05

4.35

1.40

0.875

2.880  $+0.015$

$\phi$ 3.375  $+0.001$

0.875

SHAFT END ENLARGED VIEW

NOTE:

- FOR DIRECT FLEXIBLE COUPLING
- ENCLOSURE: IP55 PROTECTION
- WITH THERMISTOR: PTC 140°C 3PCS

OUTLINE DIMENSIONS

3-PHASE INDUCTION MOTOR

MOTOR TYPE	AEHHGD-10-	FRAME NO.	447T
CUSTOMER	.	DATE	
ORDER NO.		TRANS. SHEET	TA17145A-01-04

APPD. 徐曉 11.10.17

CHKD. 林志孝 11.10.17

DWG. 李建宏 11.10.17

**東元電機股份有限公司**  
TECO Electric & Machinery Co., Ltd.  
TAIWAN

DWG NO. 31057C556440

第三角法

11

10

9

8

7

6

5

4

3

2

1