


DATE Sept. 13, 2005	OUTLINE DIMENSIONS 3-PHASE INDUCTION MOTOR	MOTOR TYPE: AEHH8B
CAT. #: HB1002		FRAME NO. 405TS

Pole	HP	kW	Hz	VOLT	Syn. Speed r/min(rpm)
2	100	75	60	460	3600
Ins	Rating	Dimension in	Approx Weight	Bearings	
F	CONT.	inches	1144 lbs.	DE: 6313C3	NDE: 6313ZC35C

Totally Enclosed Fan Cooled Type, Squirrel-cage Rotor.



Note:

1. Motor Vibration: 10μ.
2. Inpro/Seal in Both End Brackets



DWN.	K. L. KUO	01-20-05	TEC   Westinghouse	DWG NO.
CHKD.	C. H. KAO	02-02-05		31049M634630
APPD.	M. C. TSAI	02-02-05		