


TYPE	OUTPUT		POLE	TIME RATING CONT.	VOLTAGE V	Hz	SYN SPEED R.P.M
	HP.	KW.					
AEHH	200	149.2	6		460	60	1200

TOTALLY ENCLOSED FAN-COOLED TYPE, SQUIRREL-CAGE ROTOR



NOTE:

1. DIMENSIONS IN INCH
2. FRAME NO. 449T
3. F CLASS INSULATION, S.F.115
4. FOR DIRECT FLEXIBLE COUPLING
5. ENCLOSURE: IP55
6. BEARING SIZE: DRIVE END: 6320C3
NON-DRIVE END: 6316C3
7. APPROX. WEIGHT: 2880 LBS
8. NON-SPARKING FAN.
9. NOISE: BELOW 83 DBA AT 1 METER, NO LOAD.

TW-56C

DATE		OUTLINE DIMENSIONS	
06-20-05		3-PHASE INDUCTION MOTOR	
CATALOG #HH2006		Dwg NO. 3A040Y702	
CHKD. H.HUANG		REV. 00	
APPD. C.WANG			
DWN. T.H.Pan			
FEB 18 2005			
FEB 18 2005			
FEB 18 2005			

TEC Westinghouse