



### Main

Range of product	9007
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	9007T/FT
Associated head	9007CS9 9007T10S9 9007NS9 9007AS9 9007BS9 9007T5S9
Associated complete product	9007FT 9007T 9007C...S9
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 63.50 mm - offset: - convertible roller
Type of roller	1 steel outside roller (convertible) diameter: 25.40 mm - width: 6.35 mm
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Switch actuation	By 30° cam
Net weight	0.05 kg

### Environment

Ambient air temperature for operation	-23...85 °C
Ambient air temperature for storage	-23...85 °C
Environmental characteristic	Standard environment

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.032 cm
Package 1 Width	2.54 cm
Package 1 Length	8.89 cm
Package 1 Weight	104.326 g

### Offer Sustainability

Sustainable offer status	Green Premium product
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
For all Reach Rohs enquiries contact us at	<a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>

## Contractual warranty

---

Warranty

18 months

---