



Main

Device short name	C
Series name	Heavy duty

Complementary

[In] rated current	10 A
Body material	Zinc alloy
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Operating distance	0.25 inch
Operating force	3 lbf
Operating travel	2.03 Mm 0.51 mm
Switch actuation	Horizontal

Environment

Ambient air temperature for operation	-18...85 °C
Product certifications	UL listed[RETURN]CSA[RETURN]CE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.652 cm
Package 1 Width	14.732 cm
Package 1 Length	22.098 cm
Package 1 Weight	566.991 g

Offer Sustainability

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com