



Main

Device short name	C
Head type	Type C turret head rotary lever
Provided equipment	Receptacle
Series name	Heavy duty

Complementary

[In] rated current	10 A
Body material	Zinc alloy
Cable entry	12.70 mm NPT conduit entry
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Contacts type and composition	2 NO/2 NC for two stage
Maximum displacement angle	90 °
Pilot light	without pilot lamp
Specificity of operator	First stage : 10° - second stage : 2.5° Standard pre-travel
Switch actuation	CCW
Torque value	0.45 N.m
Tripping angle	4 °

Environment

Ambient air temperature for operation	-29...85 °C
Environmental characteristic	Hazardous location
Product certifications	UL listed[RETURN]CE[RETURN]CSA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.742 cm
Package 1 Width	6.985 cm
Package 1 Length	45.064 cm
Package 1 Weight	1.134 kg

Offer Sustainability

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com