



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch lever
Device short name	9007C
Associated head	9007C 9007T5 9007B 9007T10 9007N 9007A
Associated complete product	9007AW 9007C
Movement of operating head	Rotary
Type of operator	Acetal resin spring return spring rod lever length: 304.80 mm - offset: - -
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By any moving part
Net weight	0.05 kg

Environment

Ambient air temperature for operation	-29...85 °C
Ambient air temperature for storage	-29...85 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	10.2 cm
Package 1 Length	38.1 cm
Package 1 Weight	68.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------