

SG08168L05

Coded magnetic system, SWITCH PROXIMITY
MAGNET, NO, 10 VA max, 200 VDC / 0.5 A
max, 5 m cable



Main

Product or component type	Coded magnetic system
Contacts type and composition	1 NO
Material	Plastic
Electrical connection	Pre-cabled
Cable length	5 m
[Ue] rated operational voltage	200 V DC

Complementary

Protection type	Overload and short-circuit protection
Breaking capacity	10 VA

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.334 cm
Package 1 Width	19.304 cm
Package 1 Length	18.542 cm
Package 1 Weight	512.559 g

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither TWSS Holding nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.