

# ZCKD05

Limit switch head, Limit switches XC Standard, ZCKD, without lever spring return left and or right actuation

---



## Main

|                           |  |
|---------------------------|--|
| Range of product          | Telemecanique Limit switches XC Standard   |
| Series name               | Standard format  |
| Product or component type | Limit switch head  |
| Device short name         | ZCKD   |
| Head type                 | Rotary head  |
| Product compatibility     | XCKS<br>XCKM<br>XCKL   |
| Associated lever          | ZCKY39<br>ZCKY33<br>ZCKY91<br>ZCKY43<br>ZCKY59<br>ZCKY54<br>ZCKY81<br>ZCKY31<br>ZCKY55<br>ZCKY41<br>ZCKY49<br>ZCKY34 |

|                            |  |
|----------------------------|--|
| Associated body            | ZCKMD37H7<br>ZCKMD37H29<br>ZCKM1H29<br>ZCKL7H7<br>ZCKM1<br>ZCKL1<br>ZCKSD39H29<br>ZCKL8H7<br>ZCKSD37<br>ZCKM5H7<br>ZCKSD31H29<br>ZCKMD31H29<br>ZCKSD31<br>ZCKLD35H7<br>ZCKM6H29<br>ZCKLD31H7<br>ZCKMD37<br>ZCKLD39<br>ZCKS7<br>ZCKLD39H7<br>ZCKL1H7<br>ZCKM5<br>ZCKS404H29<br>ZCKMD39H29<br>ZCKS8<br>ZCKMD35<br>ZCKM9<br>ZCKS2<br>ZCKMD35H7<br>ZCKL7<br>ZCKM6<br>ZCKM8H7<br>ZCKL5<br>ZCKLD37H7<br>ZCKMD39H7<br>ZCKSD35H29<br>ZCKS7H29<br>ZCKS6H29<br>ZCKSD37H29<br>ZCKS1H29<br>ZCKL6<br>ZCKM9H29<br>ZCKM7<br>ZCKSD35<br>ZCKLD37<br>ZCKM7H29<br>ZCKS9H29<br>ZCKS9<br>ZCKMD31H7<br>ZCKS8H29<br>ZCKM6H7<br>ZCKM1H7<br>ZCKLD31<br>ZCKM8H29<br>ZCKS5<br>ZCKS1<br>ZCKL8<br>ZCKS2H29<br>ZCKL6H7<br>ZCKM7H7<br>ZCKL5H7<br>ZCKMD35H29<br>ZCKMD31<br>ZCKLD35<br>ZCKM8<br>ZCKMD39<br>ZCKS5H29<br>ZCKS6<br>ZCKM5H29<br>ZCKSD39 |
| Movement of operating head | Rotary   |
| Type of operator           | Without operating lever spring return  |
| Type of approach           | Lateral approach, 1 or 2 programmable direction  |

## Complementary

|                  |   |
|------------------|---|
| Switch actuation | From left and/or right<br>CW and/or CCW |
| Positive opening | Without<br>With                         |
| Head material    | Plastic                                 |

## Environment

|                                       |                      |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -25...70 °C          |
| Ambient air temperature for storage   | -40...70 °C          |
| Environmental characteristic          | Standard environment |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 6.400 cm  |
| Package 1 Width              | 3.400 cm  |
| Package 1 Length             | 7.700 cm  |
| Package 1 Weight             | 74.000 g  |
| Unit Type of Package 2       | S01       |
| Number of Units in Package 2 | 28        |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 15.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 2.356 kg  |
| Unit Type of Package 3       | P06       |
| Number of Units in Package 3 | 896       |
| Package 3 Height             | 75.000 cm |
| Package 3 Width              | 60.000 cm |
| Package 3 Length             | 80.000 cm |
| Package 3 Weight             | 81.108 kg |

## Offer Sustainability

|  |   |
|--|---|
| Sustainable offer status                   | Green Premium product   |
| Circularity Profile                        | No need of specific recycling operations  |
| California proposition 65                  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| For all Reach Rohs enquiries contact us at | <a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|