

Color Coding Cable Ties

Ty-Rap® Striped-Colored Cable Ties for Identification Telephone Cable Binder

Designed primarily for P.I.C. and station cable binder marking, these self-locking ties install without tools in less than 10 seconds. Compared to an installation time of 30–60 seconds using the twisted-wire method, the time saving is substantial. High-contrast color stripes extend to end of tail for instant, permanent identification of binder.



| STD. PKG. CAT. NO. | BULK. PKG. CAT. NO. | TIE COLOR | COLOR STRIPE | BODY WIDTH IN./MM | LENGTH IN./MM | TENSILE STRENGTH LBS./N | STD. PKG. QTY. | BULK PKG. QTY. |
|--------------------|---------------------|-----------|--------------|-------------------|---------------|-------------------------|----------------|----------------|
| 696-40527-0C | 696-40527-0 | Black | — | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-1-0C | 696-40527-1-0 | Brown | Black | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-1-2C | 696-40527-1-2 | Brown | Red | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-1-4C | 696-40527-1-4 | Brown | Yellow | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-1-7C | 696-40527-1-7 | Brown | Violet | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-1-9C | 696-40527-1-9 | Brown | White | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-2C | 696-40527-2 | Red | — | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-3-0C | 696-40527-3-0 | Orange | Black | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-3-2C | 696-40527-3-2 | Orange | Red | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-3-4C | 696-40527-3-4 | Orange | Yellow | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-3-7C | 696-40527-3-7 | Orange | Violet | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-3-9C | 696-40527-3-9 | Orange | White | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-4C | 696-40527-4 | Yellow | — | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-5-0C | 696-40527-5-0 | Green | Black | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-5-2C | 696-40527-5-2 | Green | Red | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-5-4C | 696-40527-5-4 | Green | Yellow | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-5-7C | 696-40527-5-7 | Green | Violet | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-5-9C | 696-40527-5-9 | Green | White | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-6-0C | 696-40527-6-0 | Blue | Black | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-6-2C | 696-40527-6-2 | Blue | Red | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-6-4C | 696-40527-6-4 | Blue | Yellow | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-6-7C | 696-40527-6-7 | Blue | Violet | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-6-9C | 696-40527-6-9 | Blue | White | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-8-0C | 696-40527-8-0 | Slate | Black | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-8-2C | 696-40527-8-2 | Slate | Red | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-8-4C | 696-40527-8-4 | Slate | Yellow | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |
| 696-40527-8-9C | 696-40527-8-9 | Slate | White | .09/2.29 | 3.62/91.95 | 18/80.07 | 50 | 1,000 |

For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).

Ty-Rap® Striped-Colored Cable Tie Kits



| STD. PKG. CAT. NO. | DESCRIPTION | STD. PKG. QTY. |
|--------------------|---|----------------|
| 650-40587 | Pouch only | 1 |
| 650-40587-1 | Pouch with Ty-Rap® cable tie assortment 1 bag each of 50 each (1,250 total) | 1 |
| 650-40587C | Cloth pouch only | 1 |
| 650-40587CF | Cloth pouch with 1 bag of 50 each Ty-Rap® cable ties (1,250 total) | 1 |
| 650-40587M | Mini pouch only | 1 |
| 650-40587MF | Mini pouch filled with assortment of Ty-Rap® cable ties (50 each) | 1 |