

Type B Liquidtight Fittings and Flexible Non-Metallic Conduits

When you have a conduit application in a liquidtight environment, it's time to load up the T&B Bullet®.

ISO Metric Bullet® Liquidtight Fitting Non-Metallic

Thomas & Betts introduces the ISO Metric Bullet® liquidtight fittings for use with the 3/8", 1/2" and 3/4" XTRA FLEX® EFC and LTC non-metallic liquidtight conduit series.

The T&B Bullet® liquidtight fitting and EFC non-metallic conduit are suited for OEM applications as in the machine tool industry where environments include continuous motion, vibration and exposure to moisture, oil, dirt and dust.

The T&B Bullet® liquidtight fitting and LTC non-metallic conduit are also suitable for construction applications where ISO metric threading and liquidtight systems are installed.

The XTRA FLEX® system offers a lightweight, liquidtight flexible conduit solution for industrial applications. The XTRA FLEX® system enables fast, easy installation and high performance in demanding industrial applications.



CAT. NO.	ANGLE OF FITTING	CONDUIT SIZE	KNOCKOUT SIZE	UNIT PACKAGE	STANDARD PACKAGE	UPC NUMBER
LT38P-ISO20	Straight	3/8"	1/2"	25	100	786210-66444
LT50P-ISO20	Straight	1/2"	1/2"	25	100	786210-66613
LT75P-ISO25	Straight	3/4"	3/4"	25	50	786210-66443
LT938P-ISO20	90°	3/8"	1/2"	25	50	786210-66612
LT950P-ISO20	90°	1/2"	1/2"	25	50	786210-66640
LT975M-ISO25	90°	3/4"	3/4"	10	50	786210-66611

*Testing: UL and CSA listed; NEMA 4, 6, 6P; IP 67 when used with LTC conduit or EFC tubing with installed T&B Bullet liquidtight fitting.