


Electrical Metallic Tubing (EMT) Fittings

Compression Connectors — Die-Cast Zinc

- ½"–4" concrete tight




CAT. NO.	CONDUIT SIZE (IN.)	DIMENSIONS (IN.)		STD. CTN.
		A	B	
<i>Non-Insulated</i>				
TC-211-SC	½	1¼	1	500
TC-212-SC	¾	1½ ₃₂	1½ ₃₂	250
TC-213-SC	1	1¾ ₆₄	1½ ₃₂	200
TC-214-SC	1¼	1¾ ₁₆	1¾ ₃₂	100
TC-215-SC	1½	1¾	2¼ ₁₆	40
TC-216-SC	2	2¾ ₃₂	2¾ ₃₂	20
TC-217-SC	2½	2¾ ₆₄	3¼	12
TC-218-SC	3	2¾	3¾ ₁₆	12
TC-219-SC	3½	2¾ ₆₄	4¾ ₁₆	10
TC-2110-SC	4	2¾ ₁₆	4¾ ₁₆	6

UL File No. E-16592 — ½"–4". CSA File No. LR-12798 — ½"–2".



CAT. NO.	CONDUIT SIZE (IN.)	DIMENSIONS (IN.)		STD. CTN.
		A	B	
<i>Insulated</i>				
TC-811-SC	½	1 ²³ / ₆₄	6 ³ / ₆₄	500
TC-812-SC	¾	1 ¹⁵ / ₃₂	1 ⁵ / ₁₆	250
TC-813-SC	1	1 ³⁵ / ₆₄	1 ¹⁵ / ₃₂	200
TC-814-SC	1¼	1 ²³ / ₃₂	1 ²⁷ / ₃₂	100
TC-815-SC	1½	1 ³¹ / ₃₂	2 ¹ / ₁₆	40
TC-816-SC	2	2¼	2 ¹ / ₃₂	20
TC-817-SC	2½	2 ²⁵ / ₃₂	3¼	12
TC-818-SC	3	2 ³¹ / ₃₂	3 ¹⁵ / ₁₆	12
TC-819-SC	3½	2 ²⁷ / ₃₂	4 ¹ / ₁₆	10
TC-8110-SC	4	2 ²³ / ₃₂	4 ¹⁵ / ₁₆	6

Offset Compression Connectors — Die-Cast Zinc




CAT. NO.	OFFSET (IN.)	CONDUIT SIZE (IN.)	DIMENSIONS (IN.)		STD. CTN.
			A	B	
TO-211SC	¾	½	2¾	1	200

UL File No. E-16592.

Capped Corner Couplings — Die-Cast Zinc

- Concrete tight when taped




CAT. NO.	CONDUIT SIZE (IN.)	DIMENSIONS (IN.)		STD. CTN.
		A	B	
TL-291	½	1.81	1.00	100
TL-292	¾	2.00	1.25	50

UL File No. E-16592.

CSA File No. LR-12798.

Compression Couplings — Die-Cast Zinc

- ½"–4" concrete tight



CAT. NO.	CONDUIT SIZE (IN.)	DIMENSIONS (IN.)		STD. CTN.
		A	B	
TK-211-SC	½	1½	1¾	500
TK-212-SC	¾	1¾	1¾	250
TK-213-SC	1	1¾	1¾	200
TK-214-SC	1¼	1¾	2¾	100
TK-215-SC	1½	2¾	2¾	40
TK-216-SC	2	2¾	2¾	20
TK-217-SC	2½	3¾	3¾	12
TK-218-SC	3	3¾	4½	12
TK-219-SC	3½	3¾	5¼	10
TK-2110-SC	4	3¾	5¼	6

UL File No. E-16592 — ½"–4".

CSA File No. LR-12798 — ½"–1¼", 2½"–4".