



## Rigid Conduit/IMC Fittings

### Locknuts — Steel/Zinc Plated




CAT. NO.	CONDUIT SIZE (IN.)	DIMENSIONS (IN.)		STD. CTN.
		A	B	
LN-100-SC	3/8	—	—	1,000
LN-101-SC	1/2	.125	1.140	1,000
LN-102	3/4	.140	1.420	1,000
LN-103	1	.170	1.770	500
LN-104	1 1/4	.170	2.281	200
LN-105	1 1/2	.170	2.598	100
LN-106	2	.187	3.175	50
LN-107	2 1/2	.375	3.562	30
LN-108	3	.375	4.250	25
LN-109	3 1/2	.438	4.803	25
LN-110	4	.438	5.402	25
LN-111	5	.500	6.674	10
LN-112	6	.561	7.934	10

### Sealing Locknuts — Steel/Zinc Plated



CAT. NO.	CONDUIT SIZE (IN.)	DIMENSIONS (IN.)		STD. CTN.
		A (MIN.)	B (MAX.)	
LS 101	1/2	.26	1.12	1,000
LS-102	3/4	.27	1.37	1,000
LS-103	1	.28	1.75	500
LS-104	1 1/4	.32	2.06	200
LS-105	1 1/2	.32	2.37	100
LS-106	2	.32	2.87	50
LS-107	2 1/2	.32	3.43	50
LS-108	3	.32	4.12	50
LS-109	3 1/2	.32	4.62	50
LS-110	4	.32	5.18	25

### Locknuts — Non-Metallic




CAT. NO.	TRADE SIZE (IN.)	A DIA. (IN.)	B THD. (IN.)	STD. CTN.
LN-501	1/2	1.3	1/2-14	100
LN-502	3/4	1.4	3/4-14	100
LN-503	1	1.7	1-11 1/2	50

Material: Nylon 6/6.

Color: Gray.


### Locknuts Die-Cast Zinc



CAT. NO.	CONDUIT SIZE (IN.)	DIMENSIONS (IN.)		STD. CTN.
		A	B	
LN-201	1/2	.125	1.140	2,000
LN-202	3/4	.140	1.420	1,000
LN-203	1	.170	1.770	1,000
LN-204	1 1/4	.170	2.281	500
LN-205	1 1/2	.170	2.598	500
LN-206	2	.187	3.175	200
LN-207	2 1/2	.375	3.562	100
LN-208	3	.375	4.250	100
LN-209	3 1/2	.438	4.803	40
LN-210	4	.438	5.402	40


CSA File No. LR- 12798.

### Grounding Locknuts — Malleable Iron/Zinc Plated



CAT. NO.	CONDUIT SIZE (IN.)	DIMENSIONS (IN.)		STD. CTN.
		A (MIN.)	B (MAX.)	
LG-401	1/2	.125	1.140	100
LG-402	3/4	.140	1.420	100
LG-403	1	.170	1.770	50
LG-404	1 1/4	.170	2.281	50
LG-405	1 1/2	.170	2.598	50
LG-406	2	.187	3.175	25
LG-407	2 1/2	.375	3.562	10
LG-408	3	.375	4.250	10
LG-409	3 1/2	.438	4.803	50
LG 410	4	.438	5.402	5

### Thin Construction Locknuts — Steel/Zinc Plated



CAT. NO.	CONDUIT SIZE (IN.)	UNIT QTY	STD. CTN.
SPLN-107	2 1/2	30	30
SPLN-108	3	25	25
SPLN-109	3 1/2	25	25
SPLN-110	4	25	25